

# PATCUT4L5

by Burndy  
Catalog ID: PATCUT4L5

Prop 65 Notice

PATRIOT 4" CU/AL SCISSOR-JAW CUTTER, 5.0 AH LITHIUM-ION BATTERY.

REFINED HYDRAULIC SYSTEM FOR SUPERIOR PERFORMANCE, SPEED AND RELIABILITY; FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS; OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; 355 degree ROTATION; Lifetime Warranty on INFINITY DRIVES 5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



## Product Details

### General

Application	Cutting
Battery Type	5.0 Ah Li-Ion
Recharge Time	0.75 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	621945471832

### Dimensions

Height	15.33 in
Length	24.31 in
Weight	20.3 lb
Width	3.26 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Cutting Capacity: Copper & Aluminum : upto 4.0" OD
-----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)