



PATMD6LIDC

by Burndy
Catalog ID: PATMD6LIDC

Prop65

In Line Tool With "D3" & BG Grooves 12V charger, 6 Tons, 18 v Li- Ion.

- Advance design high speed pump completes a crimp in approximately 2 seconds
- Pressure "pop-off" valve indicated completion of crimp
- Interchangeable scissor-action crimp jaws allow for easier access
- Uses standard "W" and "X" BURNDY® dies already in use
- Large hand grip area allows for easier operation with gloves

Features: Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics - ultimate reliability in the harshest environments, Advance design high speed pump completes a crimp in approximately 2 seconds, True one-handed operation for advance, retract and hold, 6-ton output force for reliable compression connections, Pressure pop off valve indicates completion of crimp, Interchangeable scissor action crimp jaws allow easier access to tight spaces, Ram holds position when trigger is released to allow the operator to check alignment prior to crimping, Uses standard BURNDY W and X dies already in use, Large hand grip area allows easier operation with gloves, Ergonomically balanced tool design helps lessen operator fatigue, Durable high impact formed carrying case, High capacity 2.6 AH Ni-MH batteries provide more crimps per charge 5 Year Limited Warranty on Tool, 3 year limited warranty on the batteries and charger

Product Details

General

Application	For Use on: Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact conductors, Copper Taps: #10 solid - 2/0 stranded, Aluminum and ACSR Taps: #14 solid - 4/0 ACSR, Stirrups: #6 - 4/0 ACSR, Overhead Full Tension Deadends, Full Tension Splices and Terminals #10 Str. - 4/0 ACSR, Installs splices, taps or terminations: #8 - 500 kcmil Copper Str. (YA, YA-L, YS, YS-L), #8 - 350 kcmil flex, #8 - 350 kcmil Aluminum (YA-A & YS-A)
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W and X Dies
Recharge Time	0.5 h
Sub Brand	PATRIOT® IN-LINE® CRIMPER
Tool Type	IN-LINE® Battery Actuated Scissor Action
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810529270
UPC 12 Digit	7818105292700

Dimensions

Height	4.25 in
Length	21.3 in
Weight	7.5 lb
Width	2.8 in

Electrical Ratings

Operating Voltage	18V DC
-------------------	--------

Conductor Related

Crimping Ranges	Taps:Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups:#6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals:#10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations:#8 to 500 kcmil Copper Stranded (YA, YA-L, YS, YS-L), #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum (YA-A, YS-A)
-----------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)