



PATMD6LWLCB

by Burndy
Catalog ID: PATMD6LWLCB

Prop 65 Notice

PATRIOT® IN-LINE® 6 Ton Light Weight Crimper, Permanent BG & D3 Grooves, Lanyard, Utility Bag. No Batteries or Charger Included.
Multi-AH Capability: Accepts 2.0AH, 3.0AH, 4.0AH, and 5.0AH Makita batteries.
Warranty: Lifetime on INFINITY DRIVE®, 5-year limited on tool, 3-year on batteries and charger
Tool, Crimping jaw with D3 and BG grooves

Product Details

General

Application	Crimping
Battery Type	Multi Ah Capability Li Batteries
Construction Material - Main	O
Die Type	W Dies
Sub Brand	INLINE CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945480926

Dimensions

Height	2.75 in
Length	18.70 in
Weight	6.7 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; AAC: #14 Sol. - 350 kcmil; ACSR: #14 sol. - 4/0 AWG
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)