



PATMDCUTCLWLCB

by Burndy
Catalog ID: PATMDCUTCLWLCB

Prop 65 Notice

Tool, cutting jaw with CU/AL blades; no batteries or charger

- Compact Size - Reduced weight and length
- Robust Jaw Design — Improves tool balance and user experience
- Interchangeable scissor or action crimping and cutting jaws
- 350° Rotatable Head — Allows the tool to be used in multiple positions for hard to reach areas
- LED Worklight — Lights up the work area in dimly lit spaces
- FEATURES
- 5-YEAR LIMITED WARRANTY (EXCLUDING BLADES)

Product Details

General

Application	For Cutting: Soft Drawn Copper up to 500 kcmil and Aluminum up to 636 kcmil
Type	Cutters
UPC	621945528765

Dimensions

Height	2.75 in
Length	19.42 in
Weight	7.2 lb
Width	4.375 in

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)