

# PATMDCUTLIDC

by Burndy  
Catalog ID: PATMDCUTLIDC

Prop65

Patriot In-Line Cutting Tool, 4.5 Metric Tons, Battery powered crimping tool.

- 350° head rotation
- Ergonomically balanced tool design
- Actuated blade guide automatically closes for easy positioning
- Interchangeable scissor action jaws (sold separately) available to crimp or cut with same tool

Features: Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics - ultimate reliability in the harshest environments, Advance design high speed pump completes a crimp in approximately 2 seconds, True one-handed operation for advance, retract and hold, 6-ton output force for reliable compression connections, Pressure pop-off valve indicates completion of crimp, Interchangeable scissor action crimp jaws allow easier access to tight spaces, Ram holds position when trigger is released to allow the operator to check alignment prior to crimping, Uses standard BURNDY W and X dies already in use, Large hand grip area allows easier operation with gloves, Ergonomically balanced tool design helps lessen operator fatigue, Durable high impact formed carrying case, High capacity 2.6 AH Ni-MH batteries provide more crimps per charge, 3-year limited warranty on tool, Lifetime warranty on INFINITY DRIVE, 1-year warranty on batteries and charger 5 Year Limited Warranty on Tool, 3 year warranty on the batteries and charger



## Product Details

### General

Application	For Use On: Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed, and Compact conductors, Copper Taps: #10 solid - 2/0 stranded, Aluminum and ACSR Taps: #14 solid - 4/0 ACSR, Stirrups: #6 - 4/0 ACSR, Overhead Full Tension Deadends, Full Tension Splices and Terminals #10 Str. - 4/0 ACSR, Installs splices, taps or terminations: #8 - 500 kcmil Copper Str. (YA, YA-L, YS, YS-L), #8 - 350 kcmil flex, #8 - 350 kcmil Aluminum (YA-A & YS-A)
Battery Type	3.0 Ah Li-Ion
Recharge Time	0.5 h
Sub Brand	PATRIOT® IN-LINE® CUTTER
Tool Type	IN-LINE® Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	781810552315

### Dimensions

Height	5.0 in
Length	22.0 in
Weight	8.0 lb
Width	2.7 in

### Electrical Ratings

Operating Voltage	18V DC
-------------------	--------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)