



QGFL1CB1

by Burndy
Catalog ID: QGFL1CB1

Prop 65 Notice

Copper Bartap, Cable to Drilled Bar, 10 AWG (Sol)-1 AWG (Str) Cu Cable, 230 kV, Silicon Bronze H/W.

Features: High Copper Alloy BARTAP For Joining A Range Of Cable To Bar Or Pad, One-Wrench Installation, Conductor Clamping Hardware: 3/8 IN, Wire Type: Copper, Installation Torque: 240 IN-LB

Product Details

General

Application	Substation
Connector Type	Bus Bar Clamp and Accessories
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810325131
UPC 12 Digit	7818103251311

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.13 in
Dimension - Height fraction	1-7/8 in
Dimension - Height inch	1.88 in
Dimension - Width fraction	1 in
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size Range	10 AWG-1 AWG
Conductor - Copper Str Size	#10 Sol;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;#1 Str
Conductor - Copper Str Size Range	#10 Sol-#1 Str
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)