



QP14M11X02D

by Burndy
Catalog ID: QP14M11X02D

Prop 65 Notice

Vinyl Insulated Disconnects, 14 - 16 AWG, .76 in L, .110 in W, Wire Strip Length-3/8in.

Butted seam, Funnel entry barrel opening

Product Details

General

Application	Male Disconnect
Connector Type	Male Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810530672
UPC 12 Digit	7818105306722

Dimensions

Dimension - Length Overall inch	0.76 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)