



# QPX2828Y

by Burndy  
Catalog ID: QPX2828Y

Prop 65 Notice

Universal Parallel Clamp, For Copper and Aluminum, 2 in L, 2-1/8 in W, 1/0 Str. - 4/0 Str. (Run), 1/0 Str. - 4/0 Str. (Tap).

Features: High Copper Alloy Cast Connector, Tin-Plated For Use With Copper Or Aluminum Cable, Makes Parallel, Tap, Tee, Cross Or End-To-End Connections, Edges Rounded For Easy Taping, PENETROX Joint Compound Recommended, Number Of Bolts: 2, Installation Torque: 250 IN-LB, Conductor Type: Run: Commercial Stranded Aluminum, Commercial Stranded Copper, Tap: Commercial Stranded Aluminum, Commercial Stranded Copper, Width: 2-1/8 IN, Height: 2 IN, Length: 2 IN

## Product Details

### General

|                                       |                                       |
|---------------------------------------|---------------------------------------|
| Application                           | For Use With Copper Or Aluminum Cable |
| Installation Torque Recommended in-lb | 250 LBS/in                            |
| Material                              | Copper Alloy                          |
| Material - Hardware                   | DURIUM™ Silicon Bronze                |
| Plated                                | Y                                     |
| Plating Type                          | Tin                                   |
| Sub Brand                             | VERSITAP                              |
| Trade Name                            | VERSITAP™                             |
| Type                                  | QPX-Y, Universal                      |
| UPC                                   | 781810342404                          |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Height fraction     | 2 in     |
| Dimension - Height inch         | 2.00 in  |
| Dimension - L Length Overall mm | 51 mm    |
| Dimension - Length Overall inch | 2.00 in  |
| Dimension - Width fraction      | 2-1/8 in |
| Dimension - Width inch          | 2.14 in  |
| Dimension - Width mm            | 54 mm    |

### Conductor Related

|                                  |                                 |
|----------------------------------|---------------------------------|
| Conductor - AL Str Run           | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - AL Str Run Range     | 1/0 AWG-4/0 AWG                 |
| Conductor - AL Str Tap           | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - AL Str Tap Range     | 1/0 AWG-4/0 AWG                 |
| Conductor - Copper Str Run       | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG    |
| Conductor - Copper Str Run Range | 1/0 -4/0 AWG                    |
| Conductor - Copper Str Tap       | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG    |
| Conductor - Copper Str Tap Range | 1/0 -4/0 AWG                    |

|                |   |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul> |
|----------------|---|

Certifications and Compliance

|   |    |
|---|----|
| Certification - CSA Approved            | No |
| Certification - ETL                     | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized           | No |
| Certification - cULus                   | No |
| Standards - RoHS Compliance Status      | EX |
| UL Listed                               | No |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)