



QPX3434Y

by Burndy
Catalog ID: QPX3434Y

Prop 65 Notice

Cast Cu Alloy Universal Parallel Clamp, 250 - 500 kcmil (Run), 200 - 500 kcmil (Tap)

Product Details

General

Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810343302
UPC 12 Digit	7818103433022

Dimensions

Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.88
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.54
Dimension - Width mm	65 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Run Range	250 kcmil-500 kcmil
Conductor - AL Str Tap	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Tap Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)