



QPX4444

by Burndy
Catalog ID: QPX4444

Prop 65 Notice

Parallel Clamp, Copper: 500-1000 kcmil (Run)/ 500-1000 kcmil (Tap).

Features: The Versitap Type QPX Is Recommended For Tee, Cross, Parallel, Butt And Tap Connections, Range-Taking, Only 10 Connectors Required To Accommodate Conductor Sizes From #6 AWG Stranded To 1000 KCMIL, Edges Are Rounded For Easy Taping, Made Of High Strength, High-Conductivity Copper Alloy And Silicon Bronze DURIMUM Hardware, Number Of Bolts: 4, Installation Torque: 300 IN-LB, Conductor Type: Run: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Tap: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Length: 2-5/8 IN, Height: 3-7/16 IN, Width: 2-9/16 IN

Product Details

General

Application	For Tee, Cross, Parallel, Butt And Tap Connections
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810345757
UPC 12 Digit	7818103457577

Dimensions

Dimension - Height fraction	3-7/16
Dimension - Height inch	3.44
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Width fraction	2-9/16 in
Dimension - Width inch	2.56
Dimension - Width mm	65 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil

Conductor - Copper Str Tap	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	500 kcmil-1000 kcmil
Conductor - CopperWeld Solid Run	6 AWG
Conductor - CopperWeld Solid Run Range	6 AWG
Conductor - CopperWeld Solid Tap	6 AWG
Conductor - CopperWeld Solid Tap Range	6 AWG
Conductor - Nominal Diameter	0.162, 0.813, 0.893, 0.893, 0.964, 0.998, 1.031, 1.031, 1.094, 1.151
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU Weld C Str-Run • CU Weld C Solid-Run • CU C Str-Tap • CU Weld C Str-Tap • CU Weld C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)