

QQA1C2

by Burndy
Catalog ID: QQA1C2

Prop 65 Notice

Copper Terminal, Heavy Duty, 2 Hole, 4-1 AWG (Str), 5/16" Stud, 7/8" Stud Hole Spacing, 2 Screws.

Features: Type QQA Heavy Duty, High Copper Alloy Terminal For Joining Cable To Equipment Pads Or Bar, Twin Clamping Elements Secure Joint Vibration And Flexing, One-Wrench Installation



Product Details

General

Application	For Copper Cable
Connector Type	Terminal
Installation Torque Recommended in-lb	150 LBS/in
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006092

Dimensions

Dimension - D inch	1.56 in
Dimension - F Width Center to Center inch	0.90
Dimension - Height fraction	1 in
Dimension - Height inch	1.00 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.63 in
Dimension - N inch	0.34 in
Dimension - Pad Width inch	0.63 in

Conductor Related

Conductor - Copper Str Navy Size	40 (19) Navy;50 (19) Navy;60 (37) Navy;75 (37) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy-75 (37) Navy
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Size Range	4 AWG-1 AWG

Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)