



QR1C

by Burndy
Catalog ID: QR1C

Prop 65 Notice

Splice or Reducer Qiklink, 4 Str. - 1 Str., 1-15/16 in L, 11/16 in W.

Features: High Copper Alloy Splicer/Reducer For Joining A Range Of Cable End To End, Neat, Compact Easy To Tape Installation, One-Wrench Installation, Installation Torque: 150 IN-LB, Conductor Type: Copper

Product Details

General

Application	For Joining A Range Of Copper Cable End To End
Connector Type	Splice;Reducer
Installation Torque Recommended in-lb	150 LBS/in
Material	Copper Alloy
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLINK™
Type	QR
UPC	781810334157

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Height fraction	1-1/16 in
Dimension - Height inch	1.06 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Width fraction	11/16 in
Dimension - Width inch	0.69 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - Copper Solid Size A	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size A Range	4 AWG-1 AWG
Conductor - Copper Solid Size B	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size B Range	4 AWG-1 AWG
Conductor - Copper Str Size A	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Size A Range	4 AWG-1 AWG

Conductor - Copper Str Size B	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Size B Range	4 AWG-1 AWG
Conductor Type	• CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)