



QR34

by Burndy
Catalog ID: QR34

Prop 65 Notice

Splice or Reducer, 400 - 500 kcmil, Recommended Tightening Torque:
375 IN-LB

Product Details

General

Connector Type	Splice;Reducer
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper Alloy
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLINK™
UPC	781810334690

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Height fraction	2-1/16 in
Dimension - Height inch	2.06 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.06 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.44 in
Dimension - Width mm	37 mm

Conductor Related

Conductor - Copper Str Size A	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size A Range	400 kcmil-500 kcmil
Conductor - Copper Str Size B	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size B Range	400 kcmil-500 kcmil
Conductor Type	• CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)