



QR4C

by Burndy
Catalog ID: QR4C

Prop 65 Notice

Splice or Reducer, 8 Str. - 4 Str., Recommended Tightening Torque: 110 IN-LB

Product Details

General

Connector Type	Splice;Reducer
Installation Torque Recommended in-lb	110 LBS/in
Material	Copper Alloy
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLINK™
UPC	781810334249

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Height fraction	13/16 in
Dimension - Height inch	0.81 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	5/8 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - Copper Solid Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size A Range	8 AWG-4 AWG
Conductor - Copper Solid Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size B Range	8 AWG-4 AWG
Conductor - Copper Str Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size A Range	8 AWG-4 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size B Range	8 AWG-4 AWG

Conductor Type	• CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	54
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)