



## RDM628

by Burndy  
Catalog ID: RDM628

Prop 65 Notice

URD Mole, #4 Str. - 250 kcmil Al or Cu 300 kcmil - 350 kcmil , 600 Volt Rating, 8.78 in L.

Features: Type RDM-28 MOLE Is An Economical, Insulated, Submersible Service Junction Suitable For Direct Burial Or For Use In Enclosures, Disconnectable Joints Allow Additions Of New Services Without Disturbing Previous Installations, Taping Is Eliminated, Heat-Shrink Or Force-Fit Rubber Sleeves Insulate Each Joint, Rubber Is Used To Insulate The MOLE Body, Removable Sealing Covers Are Supplied On All Outlets But Two, REA Listed Tap Kits, Including HYLUG, Hardware And Sleeve Are Ordered Separately, Number Of Outlets: 6

## Product Details

### General

Application	For Aluminum And Copper And Direct Burial Or For Use In Enclosures
Connector Type	Tap
Insulation	Y
Insulation Type	Rubber
Material	Aluminum Alloy
Number Of Outlets	6
Sub Brand	URD MOLE
Trade Name	MOLE™
Type	RDM-28
UPC	781810180051
UPC 12 Digit	7818101800511

### Dimensions

Dimension - Length Overall inch	8.78 in
---------------------------------	---------

### Conductor Related

Conductor - AL Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Size Range	4 AWG-350 kcmil
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	4 AWG-250 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)