



RDM728T

by Burndy
Catalog ID: RDM728T

URD MOLE, #12 Sol - 350 kcmil(6 Outlets) & 350 - 500 kcmil(1 Outlet)

Product Details

General

Connector Type	Mole
Insulation	Y
Insulation Type	Vinyl
Material	Aluminum Alloy
Number Of Outlets	7
Plated	Y
Plating Type	Tin
Trade Name	MOLE™
UPC	781810180204
UPC 12 Digit	7818101802044

Dimensions

Dimension - Length Overall inch	11.53 in
---------------------------------	----------

Conductor Related

Conductor - AL Str Run	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	4 AWG-350 kcmil
Conductor - Copper Str Run	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	4 AWG-4/0 AWG
Conductor - Copper Str Tap	500 kcmil
Conductor - Copper Str Tap Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)