



RYA26UCR

by Burndy
Catalog ID: RYA26UCR

Prop 65 Notice

Force Fit Tap Kit, Al 2/0 STR 3/0 Sol, Cu 2/0 Sol.

Features: The Kit Consists Of: Universal HYLUG, Mounting Hardware And Pre-Lubricated Forcefit Rubber Sleeve, The HYLUG Is Pre-Filled With PENETROX Joint Compound And Sealed, Installed With Common Installation Tools, Three Die Sets Install A Range Of 4 AWG Stranded - 350 MCM, The Rubber Sleeve Has Internal Sealing Rings That Provide A Positive Moisture Seal By Exerting Circumferential Force On Cable And MOLE Insulation, Pre-Lubricating Sleeve Makes Installation Easier, REA Listed, No Trimming Required, Eei Die Index: 11A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6 Series Tool, W249 Die, (3), WK840 Die, (5), Y39, Y35, Y750 Series Tool, U249 Die, (2) Overlap Crimps, UK840T Die, (4), OUR840 Tool, X249 Die, (6), X840 Die, (5), Die Index: 249 Or 840

Product Details

General

Application	FOR ALUMINUM OR COPPER FOR USE WITH TYPE RDM-28 URD MOLE
Connector Type	Terminal
Die Index	249;K-840
Insulation	Y
Insulation Type	Rubber
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
Sub Brand	TAP KITS, MOLE
Trade Name	MOLE™
Type	RYA-UCR
UPC	781810181850

Dimensions

Dimension - B Length inch	1.5 in
Dimension - D inch	0.91 in
Dimension - Length Overall inch	2.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-9/16

Conductor Related

Conductor - AL Str Size	2/0;3/0
Conductor - Copper Solid Size	2/0

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)