



RYA2UCR

by Burndy
Catalog ID: RYA2UCR

Prop 65 Notice

MOLE™ tap kits, consists of Universal HYLUG™, mounting hardware and pre-lubricated forcefit rubber sleeve.

Product Details

General

Connector Type	Terminal
Die Index	243;BG
Insulation	Y
Insulation Type	Rubber
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
Trade Name	MOLE™
UPC	781810181751

Dimensions

Dimension - B Length inch	0.96 in
Dimension - D inch	0.65 in
Dimension - Length Overall inch	2 in
Dimension - Pad Width inch	0.65 in
Dimension - Strip Length inch	1-1/16

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG
Conductor - Copper Solid Size	1 AWG
Conductor - Copper Solid Size Range	1 AWG
Conductor - Copper Str Size	2 AWG;1 AWG
Conductor - Copper Str Size Range	2 AWG-1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)