



S4P28A

by Burndy
Catalog ID: S4P28A

Prop 65 Notice

Cast Al Alloy Span Tap Connector, #2-4/0 Str(Cu,Al)(Run), 6 Sol- 1/0 Str(Cu, Al)(Tap), Case: High Density Weather Resistant Polyethylene.

Connector supply prefilled with Penetrox and sealed

Product Details

General

Application	Used for any combinations of aluminium or copper cables in any areas where use of aluminium conductor is an accepted practice
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Sub Brand	SPANTAP
Type	Span Tap Phase Connector
UPC	781810036907
UPC 12 Digit	7818100369077

Electrical Ratings

Rating - KVA	550 kV
--------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)