



SB232TC38

by Burndy
Catalog ID: SB232TC38

Prop 65 Notice

HANDYBUG 3/8" HARDWARE, COPPER CONDUCTOR RANGE: 8 AWG - 2 AWG, TIN-PLATED COPPER ALLOYSS, stud Dia: 3/8 - 16.

Can be used for splicing and tap connections, No special tooling required.

Product Details

General

Application	Power or Grounding and Bonding Applications
Material	Copper Alloy, Tin Plated
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	150 in-lbs
Sub Brand	HANDYBUG
Trade Name	SUPERBUG
Type	HandyBug
UPC	781810677414
UPC 12 Digit	7818106774144

Dimensions

Dimension - L Length Overall mm	0 mm
Dimension - Thread Size	-
Dimension - Width mm	0 mm

Conductor Related

Conductor Range	#8 AWG to #2 AWG
-----------------	------------------

Certifications and Compliance

Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)