



SNM18

by Burndy
Catalog ID: SNM18

Prop 65 Notice

Cu Butt Splice, Smooth Funnel Entry, W/InspWindow, AN22-18, 600 V, 1.53" L, Nylon Insul, Integral bbl, Tin Plated, Red.

Features: The Type SNM INSULINK Is A High Quality Nylon Insulated Butt Splice Designed To Meet Military MS25181, Class 1 Requirements, Manufactured From Tin Plated, Seamless Copper Tubing With An Integral Barrel/Insulation Grip: Provides Maximum Tensile Strength, Plus Excellent Cable Support And Strain Relief, Smooth Funnel Entry: Provides Easy Wire Insertion, Transparent Nylon Insulation: Permits Easy Wire Inspection, External Ring Locator: Provides Proper Tool Alignment For Correct Crimp, Insulation Support: No, Installation Tool: Plier Type: Y10D Tool, Ratchet: MR8-83, MR8-85, MS25037 Tool, Conductor Type: Commercial/Aircraft Stranded Copper, Color Code: Red, Wire Strip Length: 7/32 IN

Product Details

General

Application	The type SNM INSULINK is a high quality nylon insulated butt splice designed to meet military MS25181, class 1 requirements.
Color Code	Red
Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	SNM
UPC	781810736609
UPC 12 Digit	7818107366099

Dimensions

Cable Insulation Diameter Maximum	0.120 in
Dimension - Diameter Max Size inch	0.12 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.53 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Strip Length inch	7/32 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	22 - 18 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)