

# SP14BG25

by Burndy  
Catalog ID: SP14BG25



Electrolytic Copper Butt Splice, 16 - 14 AWG, 600 V, Tin Plated.

Features: The Type SP VINYLINK Is A PVC Insulated Seamless Butt Splice, Type SP VINYLINK Is Designed To Accommodate A Broad Range Of 600 Volt Cables, Manufactured From Seamless Electrolytic Copper Tubing: Provides Maximum Conductivity And Tensile Strength, In A High Quality Design With NO Seams To Split, Funnel Entry: Provides Easy Wire Insertion, Electro-Tin Plated: Provides Durable Long Lasting Resistance To Corrosion, Expanded Insulation Support: Lower Inventory Requirements, Red Wire Range Of 22-16: Lower Inventory Requirements, Vinyl Insulator: Economical Means Of Providing High Dielectric Values And Cable Insulation Support, Insulation Support: Yes, Package: 25/Bag, Conductor Type: Commercial/Aircraft Stranded Copper, Installation Tool: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: MR8G98, MR8-89-1, MR15 Tool, Color Code: Blue, Wire Strip Length: 1/4 IN

## Product Details

### General

Application	For Accommodating A Broad Range Of 600 Volt Cables
Color Code	Blue
Connector Type	Splice
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Polyvinylchloride
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Temperature Rating	105° C
Trade Name	VINYLINK™
Type	SP
UPC	781810486290
UPC 12 Digit	7818104862900

### Dimensions

Dimension - Diameter Max Size inch	0.18 in
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1/4 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 - 14 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)