



T1012

by Burndy
Catalog ID: T1012

Ring Tongue Terminal, Polyvinylchloride, 600 VOLTS MAX. 105 Deg C MAX.,Stud size:1/2.

Features: Constructed of pure electrolytic copper, Long brazed seam barrel and deep V groove inner serrations

Product Details

General

Application	For Control Wiring And Other Standard Duty Applications
Connector Type	Terminal
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYDENT
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810525630
UPC 12 Digit	7818105256300

Dimensions

Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.21 in
Dimension - Pad Width inch	0.69 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.61 in

Conductor Related

Conductor - Copper Solid Size	22
Conductor - Copper Solid Size Range	22
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)