

T106

by Burndy
Catalog ID: T106

Prop 65 Notice

Copper Compression Terminal, Ring Tongue, 12-10 AWG, #4-#6 Stud, Long Barrel, Tin Plated



Product Details

General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722008
UPC 12 Digit	7818107220088

Dimensions

Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.37 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.29 in

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG

Conductor Type	• CU C Solid-Size • CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)