



T148F

by Burndy
Catalog ID: T148F

Prop 65 Notice

Copper Compression Terminal, Fork Tongue, 20-14 AWG, #6-#8 Stud, Long Barrel, Tin Plated.

Features: Type T-F Is Constructed In The Same Manner As The Type "T" And Employs A Fork Tongue, The Fork Permits Rapid Installation Of The Terminal Under A Screw Head Without Completely Removing The Screw, Two Or More Terminals May Be Stacked Easily On A Common Stud, Bulk Catalog Number: YAD18-8F, Wire Insulation Grip: No, Wire Strip Length: 9/32 IN, Installation Tool: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: Y8MRB-1, MR20, MR8G98 Tool, Finish: Electro-Tin Plated

Product Details

General

Application	For Control Wiring And Other Standard Duty Applications
Connector Type	Compression Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	T-F
UPC	781810722381
UPC 12 Digit	7818107223811

Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Diameter Max Size inch	0.07 in
Dimension - Hole Size fraction	1/6
Dimension - Hole Size inch	0.18 in
Dimension - L Length Overall mm	19
Dimension - Length Overall inch	0.73 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z inch	0.27 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
-----------------	--------------------

Conductor Type	• CU C Solid-Size • CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)