

T184

by Burndy
Catalog ID: T184

Prop 65 Notice

Copper Compression Terminal, Ring Tongue, 22-18 AWG, #3-#4 Stud, Long Barrel, Tin Plated.

Provides maximum conductivity, Low resistance and ductility for excellent crimp forming properties, Provides durable long-lasting corrosion resistance, Provides an easy visual check of wire insertion, Wire range is clearly marked on terminal



Product Details

General

Application	For Control Wiring And Other Standard Duty Applications
Connector Type	Compression Terminal
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810723005
UPC 12 Digit	7818107230055

Dimensions

Dimension - Hole Size fraction	1/8
Dimension - Hole Size inch	0.12 in
Dimension - L Length Overall mm	16
Dimension - Length Overall inch	0.64 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#3 - #4
Dimension - Z inch	0.26 in

Conductor Related

Conductor Range	#22 AWG to #18 AWG
-----------------	--------------------

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)