



# TFV3B6V2

by Burndy  
Catalog ID: TFV3B6V2

Polyethylene Hook and Loop Straps, Black , 6.00" L, 3/4" W, Used On Fiberoptic Applications.

- Hook and Loop Cable Tie

Features: Reusable And Flexible BURNDY Hook And Loop Straps Are A Unique Self-Gripping Fastening System, These Ties Are Specifically Used On Fiberoptic Applications, The TFV-V2 Flame Retardant Straps Are UL Listed Wire Positioning Devices (ZODZ), UL94-V2 Rated For Use In Air Handling Spaces In Accordance With The Necsection 300-22 (C) And (D), Perfect For Plenum Areas, 25 Straps Are Conveniently Packaged In Each Polybag, Average Sheer: 23 PSI, Average Peel: 0.6 PIW

## Product Details

### General

|             |                                                              |
|-------------|--------------------------------------------------------------|
| Application | For Used On Fiberoptic Applications,Perfect For Plenum Areas |
| Color       | Black                                                        |
| Material    | Polyethylene & Nylon                                         |
| Sub Brand   | UNIRAP                                                       |
| Type        | TFV-B, Flame Retardant                                       |
| UPC         | 781810445495                                                 |

### Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1       |
| Dimension - L Length Overall mm      | 152 mm  |
| Dimension - Length Overall inch      | 6.00 in |
| Dimension - Width inch               | 0.50 in |
| Dimension - Width mm                 | 13 mm   |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - 94V0 Rated         | Y  |
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - UV Rated           | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)