



## TMHG42

by Burndy  
Catalog ID: TMHG42

Prop 65 Notice

Stainless Steel Hardware Kit For I-Beam Connector, 1/2" Screw, 0.42" Max. Terminal Pad Thickness.

GROUNDLINK connectors are made of high-conductivity wrought copper and come pre-filled with PENETROX E compound and strip sealed. Order terminal mounting hardware separately.

## Product Details

### General

Application	An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (para llel) beam.
Connector Type	Hardware
Material	Stainless Steel
Sub Brand	INSULUG
Type	Compression Ground Connector
UPC	781810035054
UPC 12 Digit	7818100350544

### Dimensions

Dimension - Thread Size	1/2 - 13
-------------------------	----------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL 486A-B</li> <li>IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>UL 486A-B</li> <li>IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)