

# TP1010FBG25

by Burndy  
Catalog ID: TP1010FBG25

Cu Fork Tongue Terminal, Smooth Entry, 10-12 AWG, 600 V, #10 Spade, 1.07" L, 0.41" W, Vinyl Insul, Tin Plated, Yellow(Insul Color), 25 Pcs./Bag.

Features: The Type TP-F Is A Fork Tongue Variation Of The TP Design And Makes Installation Easier, 600 V Maximum, 105 DEG C Max, Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, Insulation Diameter (maximum): 0.26 IN, Bulk Catalog Number: BA10EF10, Temperature Rating: 105 DEG C Maximum, Package: 25/Bag, Tape Mounted Catalog Number: BA10EF10M, Installation Tool: MR15, M8ND Tool With N10ET-23 Die, Color Code: Yellow, Wire Strip Length: 19/64 IN, Finish: Electro-Tin Plated, Wire Insulation Grip: No



## Product Details

### General

Application	The Type TP-F is a fork tongue variation of the TP design and makes installation easier
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	TP-F
UPC	781810486337
UPC 12 Digit	7818104863377

### Dimensions

Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.07 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.31 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)