



TP1014F

by Burndy
Catalog ID: TP1014F

Copper Terminal, Fork Tongue, 12-10 AWG, 1/4" Stud, Vinyl Insulated, Tin Plated, Wire strip Length: 19/64"

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	VINYLUG™
UPC	621945047105
UPC 12 Digit	6219450471055

Dimensions

Cable Insulation Diameter Maximum	0.260 in
Dimension - Hole Size fraction	13/50
Dimension - Hole Size inch	0.26 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.26 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.46 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)