



# **TP106F**

by Burndy Catalog ID: TP106F

Prop 65 Notice

Copper Terminal, Fork Tongue, 12-10 AWG, #4-#6 Stud, Vinyl Insulated, Tin Plated.

Features: The Type TP-F Is A Fork Tongue Variation Of The TP Design And Makes Installation Easier, 600 V Maximum, 105 DEG C Max, Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, Temperature Rating: 105 DEG C Maximum, Bulk Catalog Number: BA10EF6, Insulation Diameter (maximum): 0.26 IN, Installation Tool: MR15, M8ND Tool With N10ET-23 Die, Tape Mounted Catalog Number: BA10EF6M, Color Code: Yellow, Wire Strip Length: 19/64 IN, Wire Insulation Grip: No, Finish: Electro-Tin Plated

## **Product Details**

#### General

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Туре	TP-F
UPC	781810710487
UPC 12 Digit	7818107104877

#### **Dimensions**

Cable Insulation Diameter Maximum	0.260 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#6
Dimension - Z inch	0.26 in

## **Electrical Ratings**

tage - Maximum	600 V
----------------	-------

#### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

### Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

### For further technical assistance, please contact us

### **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)