



TP14516

by Burndy Catalog ID: TP14516

Prop 65 Notice

Copper Terminal, Ring Tongue, 16-14 AWG, $5/16^{\prime\prime}$ Stud, Vinyl Insulated, Tin Plated.

Expanded insulation support accepts standard and large wire diameters, Easy wire insertion, It Provides durable long-lasting corrosion resistance.

Product Details

General

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Color Code	Blue
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	COMPRESSION TERMINAL, VINYLUG
Trade Name	VINYLUG™
Туре	Ring Tongue
UPC	781810103111
UPC 12 Digit	7818101031111

Dimensions

Cable Insulation Diameter Maximum	0.190 in
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Diameter Max Size inch	0.19 in
Dimension - Hole Size fraction	1/3
Dimension - Hole Size inch	0.33 in
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.21 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	5/16 in
Dimension - Z inch	0.45 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Type	CU C Solid-Size CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)