



## U25RT

by Burndy  
Catalog ID: U25RT

Prop 65 Notice

Stainless Steel Circular Butting Twin Die, U die, 1/0 Str Cu, Pink, Index 12

Features: Fits Y35, Y39, Y750HS, PAT750, PAT750XT-18V, PAT46-18V, Y46 (With PUADP-1 Adapter)

## Product Details

### General

|                              |  |
|------------------------------|--|
| Application                  | Crimping   |
| Application - For Use On     | Fit in Y35, Y39, Y750, PAT 750 Tools Series; Fit in Y46 (with PUADP-1 Adapter), PAT46 Tools series; Fit in Y45 (With PT6515 Adapter) |
| Color Code                   | Pink   |
| Construction Material - Main | Stainless Steel  |
| Crimp Force Capacity         | 12 ton   |
| Die Index                    | 12   |
| Die Type                     | U DIE  |
| Material                     | Stainless Steel  |
| Sub Brand                    | U-DIE  |
| UPC                          | 781810627334   |
| UPC 12 Digit                 | 7818106273344  |

### Dimensions

|                        |         |
|------------------------|---------|
| Dimension - Width inch | 1       |
| Dimension - Width mm   | 25      |
| Weight                 | 0.45 lb |

### Conductor Related

|                 |         |
|-----------------|---------|
| Crimping Ranges | 1/0 AWG |
|-----------------|---------|

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed                          | No |

### Logistics

|                       |              |
|-----------------------|--------------|
| Minimum Pack Quantity | 1            |
| Package Contents      | Die set only |

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)