

## UC25R2RS

by Burndy  
Catalog ID: UC25R2RS

Prop 65 Notice

High strength, high conductivity aluminum alloy. Properly proportioned to minimize stress corrosion and deterioration by galvanic action, Wrench: 1/2.

Features: High Strength, High Conductivity, Non-Copper Bearing Aluminum Alloy, Properly Proportioned To Minimize Stress Corrosion And Deterioration By Galvanic Action, Keying Tabs On Connector Body Halves Prevent Mismatching, Square Shank, High Strength Galvanized Steel Bolt Allows One Wrench Installation, Also Supplied Pre-Filled With PENETROX Joint Compound And Stripsealed, Length: 1-1/8 IN, Width: 1-3/8 IN, Height: 1-5/8 IN



## Product Details

### General

Application	For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005
Installation Torque Recommended in-lb	180 in-lb
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Trade Name	TAPIT™
Type	UC-RS
UPC	781810093009
UPC 12 Digit	7818100930099

### Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.125 in
Dimension - Height fraction	1-5/8 in
Dimension - Height inch	1.68 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.47 in
Dimension - Width mm	37 mm

### Conductor Related

Conductor - AAAC 5005 Size A Range	6 AWG-1/0 AWG
Conductor - AAAC 5005 Size B Range	6 AWG-1/0 AWG
Conductor - AAAC 6201 Size A Range	6 AWG-1/0 AWG
Conductor - AAAC 6201 Size B Range	6 AWG-1/0 AWG
Conductor - AL Str Size A	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size A Range	8 AWG-1/0 AWG
Conductor - AL Str Size B	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG

Conductor - AL Str Size B Range	8 AWG-2 AWG
Conductor - Copper Solid Size A	8 AWG
Conductor - Copper Solid Size A Range	8 AWG
Conductor - Copper Solid Size B	8 AWG
Conductor - Copper Solid Size B Range	8 AWG
Conductor - Copper Str Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size A Range	8 AWG-1/0 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size B Range	8 AWG-2 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)