



UC25R2R

by Burndy
Catalog ID: UC25R2R

Prop 65 Notice

Cast Aluminum Alloy TAPIT™, 8 (SOL.) AWG-1/0 (Str.) AL & CU (Groove A), 6 AWG-1/0 AWG ACSR(Groove A), 8 (SOL.) AWG-2 (Str.) AWG CU (Groove B), 8 AWG-1 AWG ACSR (Groove B)

Product Details

General

Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810092804
UPC 12 Digit	7818100928044

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.125 in
Dimension - Height fraction	1-5/8 in
Dimension - Height inch	1.66 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.45 in
Dimension - Width mm	37 mm

Conductor Related

Conductor - ACSR Str Run Range	6 AWG-1/0 AWG
Conductor - AL Str Size A Range	8 AWG-1/0 AWG
Conductor - AL Str Size B Range	8 AWG-1/0 AWG
Conductor - Copper Str Size A Range	8 AWG-1/0 AWG
Conductor - Copper Str Size B Range	8 AWG-1/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)