



UC28RS

by Burndy
Catalog ID: UC28RS

Prop 65 Notice

High strength, high conductivity aluminum alloy. Properly proportioned to minimize stress corrosion and deterioration by galvanic action, Wrench: 9/16.

Features: High Strength, High Conductivity, Non-Copper Bearing Aluminum Alloy, Properly Proportioned To Minimize Stress Corrosion And Deterioration By Galvanic Action, Keying Tabs On Connector Body Halves Prevent Mismatching, Square Shank, High Strength Galvanized Steel Bolt Allows One Wrench Installation, Also Supplied Pre-Filled With PENETROX Joint Compound And Stripsealed, Length: 1-3/8 IN, Width: 1-7/8 IN, Height: 2-3/8 IN

Product Details

General

Application	For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005
Installation Torque Recommended in-lb	240 in-lb
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Trade Name	TAPIT™
Type	UC-RS
UPC	781810095805
UPC 12 Digit	7818100958055

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.375 in
Dimension - Height fraction	2-3/8 in
Dimension - Height inch	2.33 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.87 in
Dimension - Width mm	47 mm

Conductor Related

Conductor - AAAC 5005 Size A Range	1/0 AWG-4/0 AWG
Conductor - AAAC 5005 Size B Range	6 AWG-1/0 AWG
Conductor - AAAC 6201 Size A Range	1/0 AWG-4/0 AWG
Conductor - AAAC 6201 Size B Range	6 AWG-1/0 AWG
Conductor - AL Str Size A	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size A Range	1/0 AWG-4/0 AWG
Conductor - AL Str Size B	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG

Conductor - AL Str Size B Range	8 AWG-1/0 AWG
Conductor - Copper Solid Size B	8 AWG
Conductor - Copper Str Size A	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size A Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Str Size B Range	8 AWG-1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)