



UC2W30

by Burndy
Catalog ID: UC2W30

Prop 65 Notice

CU Parallel Groove Clamp accommodates large number of CU Conductors, Conductor: 2 Sol. - 300 (Either Groove).

Features: Type UC Connector Accommodates Large Range Of Conductors In Either Groove, Reducing Inventory To A Minimum, Interlocking Finger Design Provides Firm Grip With Maximum Contact Length, High Strength, Corrosion Resistant Silicone Bronze Hardware, One Wrench Installation, Width: 2 IN, Length: 2-3/8 IN, Height: 2-1/8 IN

Product Details

General

Application	For Range Of Copper
Installation Torque Recommended in-lb	240 LBS/in
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Type	UC
UPC	781810012871

Dimensions

Dimension - B Length fraction	2-7/8 in
Dimension - B Length inch	2.88 in
Dimension - Height fraction	2-3/16 in
Dimension - Height inch	2.18 in
Dimension - Width fraction	2 in

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	2 AWG-300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)