



UC3040

by Burndy
Catalog ID: UC3040

Prop 65 Notice

CU Parallel Groove Clamp accommodates large number of CU
Conductors, Conductor: 300 - 800 (Either Groove)

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Plated	N
Plating Type	Unplated
UPC	781810012918

Dimensions

Dimension - B Length fraction	4-1/4 in
Dimension - B Length inch	4.25 in
Dimension - Height fraction	3-5/16 in
Dimension - Height inch	3.31 in
Dimension - Width fraction	3-1/16 in
Dimension - Width inch	3.06 in

Conductor Related

Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	300 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)