



UCG28R

by Burndy
Catalog ID: UCG28R

Parallel Clamp, Cast Aluminium Alloy, 2.20" L, 2.75" Height, 2.20" W

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810111086

Dimensions

Dimension - B Length fraction	2-1/5 in
Dimension - B Length inch	2.20 in
Dimension - Height fraction	2-3/4 in
Dimension - Height inch	2.75 in
Dimension - Width fraction	2-1/5 in
Dimension - Width inch	2.20 in

Conductor Related

Conductor - AAAC 5005 Size A	123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 5005 Size A Range	123.3 (7) kcmil-394.5 (19) kcmil
Conductor - AAAC 5005 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size A	123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 6201 Size A Range	123.3 (7) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Size B Range	123.3 (7) kcmil-394.5 (19) kcmil
Conductor - AL Str Size A	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size A Range	1/0 AWG-4/0 AWG
Conductor - AL Str Size B	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size B Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size A	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG

Conductor - Copper Str Size A Range	1/0 -4/0 AWG
Conductor - Copper Str Size B	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size B Range	1/0 -4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size A • CU C Solid-Size A • CU C Str-Size A • AAAC C 5005-Size A • AAAC C 6201-Size A • AL C Str-Size B • CU C Solid-Size B • CU C Str-Size B • AAAC C 5005-Size B • AAAC C 6201-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)