



UCG32RS

by Burndy
Catalog ID: UCG32RS

Prop 65 Notice

Multiple purpose parallel groove clamp made of high strength, high conductivity aluminum alloy. Hardware allows for one of two wrench installation, length: 1-1/2", width: 2-1/8".

Features: Multiple Purpose Parallel Groove Clamp Made Of High Strength, High Conductivity, Non Copper Bearing Aluminum Alloy, Properly Proportioned To Minimize Stress Corrosion And Deterioration By Galvanic Action, Interlocking Fingers On Connector Body Halves Prevent Mismatching, Square Shank, Hex Head, Round Collar, High Strength Galvanized Steel Bolt Allows One Or Two-Wrench Installation, Also Supplied Pre-Filled With PENETROX Joint Compound And Stripsealed, Width: 2-1/8 IN, Length: 1-1/2 IN, Height: 2-5/8 IN

Product Details

General

Application	For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Trade Name	TAPIT™
Type	UCG-RS
UPC	781810097953
UPC 12 Digit	7818100979533

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Height fraction	2-3/5 in
Dimension - Height inch	2.59 in
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.12 in
Dimension - Width mm	54 mm

Conductor Related

Conductor - AAAC 5005 Size A	123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 5005 Size A Range	123.3 (7) kcmil-394.5 (19) kcmil
Conductor - AAAC 5005 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 5005 Size B Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Size A	123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 6201 Size A Range	123.3 (7) kcmil-394.5 (19) kcmil

Conductor - AAAC 6201 Size B	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 6201 Size B Range	123.3 (7) kcmil-394.5 (19) kcmil
Conductor - ACSR Str Size Range	1/0 AWG - 336.5 Kcmil
Conductor - AL Str Size A	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil
Conductor - AL Str Size A Range	1/0 AWG - 397.5 Kcmil
Conductor - AL Str Size B	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size B Range	8 AWG- 2/0 AWG
Conductor - Copper Str Size A Range	1/0 AWG - 397.5 Kcmil
Conductor - Copper Str Size B Range	8 AWG- 2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size A • CU C Solid-Size A • CU C Str-Size A • AAAC C 5005-Size A • AAAC C 6201-Size A • AL C Str-Size B • CU C Solid-Size B • CU C Str-Size B • AAAC C 5005-Size B • AAAC C 6201-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)