



## UCK1UL

by Burndy  
Catalog ID: UCK1UL

Interlocking finger design accommodates large range of conductor sizes. Tin-plated, cast of high copper alloy and clamped with silicon bronze DURUM bolt, wrench size: 1/2.

Features: Interlocking Finger Design Accommodates Large Range Of Conductor Sizes, Tin-Plated, Cast Of High Copper Alloy And Clamped With Silicon Bronze DURUM Bolt, PENETROX Joint Compound Recommended With ACSR, Applications Include Grounding For The Cable TV Industry, Stud/bolt Size: 5/16 IN, Installation Torque: 75 IN-LB, Width: 1-7/16 IN, Length: 1 IN, Height: 1-7/16 IN

## Product Details

### General

Application	For Use With Aluminum Or Galvanized Steel Strand To Copper Or Copper Bonded Steel Wire, Grounding For The Cable TV Industry
Installation Torque Recommended in-lb	180 LBS/in
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TAPIT
Type	UC-K, Universal
UPC	781810120750
UPC 12 Digit	7818101207500

### Dimensions

Dimension - Height fraction	1-7/16 in
Dimension - Height inch	1.4375 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.4375 in
Dimension - Width mm	37 mm

### Conductor Related

Conductor - Copper Solid Size B	6 Sol
Conductor - Copper Str Size B	6 Str
Conductor - Galvanized Steel Str Size Range	1/4 in -5/16 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)