



# UCT26RSHN

by Burndy  
Catalog ID: UCT26RSHN

Prop 65 Notice

Aluminum Parallel Groove Clamp with Shear nut, Run: Cu & AL: 8 Sol. - 2/0, ACSR: 6 - 2/0, Tap: Cu & AL: 6 Sol. - 2/0, ACSR: 6 - 2/0

## Product Details

### General

|              |               |
|--------------|---------------|
| Material     | Aluminum      |
| Plated       | N             |
| Plating Type | Unplated      |
| Trade Name   | FASTAP™       |
| UPC 12 Digit | 7818106437855 |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 2.62 in |
| Dimension - Length Overall inch | 1.62 in |
| Dimension - Width inch          | 2.50 in |

### Conductor Related

|                                     |                   |
|-------------------------------------|-------------------|
| Conductor - AAAC 5005 Size          | 6 STR - 2/0 STR   |
| Conductor - AAAC 5005 Size Range    | 6 STR - 2/0 STR   |
| Conductor - AAAC 6201 Size          | 6 STR - 2/0 STR   |
| Conductor - AAAC 6201 Size Range    | 6 STR - 2/0 STR   |
| Conductor - ACSR Str Size           | 6 STR - 2/0 STR   |
| Conductor - ACSR Str Size A Range   | 6 Str. - 2/0      |
| Conductor - ACSR Str Size B Range   | 6 Str. - 2/0      |
| Conductor - AL Str Size A           | 8 SOL - 2/0 STR   |
| Conductor - AL Str Size A Range     | 8 Sol. 2/0        |
| Conductor - AL Str Size B           | 8 SOL - 2/0 STR   |
| Conductor - AL Str Size B Range     | 8 Sol. - 2/0 Str. |
| Conductor - Copper Solid Size       | #8 - 2/0          |
| Conductor - Copper Solid Size Range | #8 - 2/0          |
| Conductor - Copper Str Size A Range | 8 Sol. 2/0        |
| Conductor - Copper Str Size B Range | 8 Sol. - 2/0 Str. |

|                |                                                                                                                                                                                                                                                                                          |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Type | <ul style="list-style-type: none"><li>• AAAC C 5005-Size</li><li>• AAAC C 6201-Size</li><li>• ACSR C Str-Size</li><li>• AL C Str-Size A</li><li>• AL C Str-Size B</li><li>• CU C Solid-Size</li><li>• CU C Str-Size A</li><li>• CU C Str-Size B</li><li>• CU Weld C Solid-Size</li></ul> |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | UI |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)