

UGS350ULDB

by Burndy
Catalog ID: UGS350ULDB

Prop 65 Notice

In-Line Splice/Reducer For Direct Burial, 12 AWG - 350 kcmil, 5/16", Dual rated AL9CU for CU or AL.

Features: EPDM Rubber Covered 6061-T6 Aluminum Connector, Dual Rated AL9CU For Copper Or Aluminum Conductor, UL Listed And CSA Certified For Direct Burial, Broad Range Taking Capability, Low Installation Cost, Installation Torque: 350 IN-LB, Number Of Screws: 2, Hex Size: 5/16 IN



Product Details

General

Application	For Direct Burial
Connector Type	Splice;Reducer
Hex Size	5/16
Installation Torque Recommended in-lb	350 LBS/in
Insulation	Y
Insulation Type	Rubber
Material	Brass
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SPLICE KIT
Temperature Rating	194
Trade Name	UNITAP™
Type	In-Line, Underground
UPC	781810343807

Dimensions

Dimension - Height fraction	2.833333333333335 in
Dimension - Height inch	2.81 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.50 in
Dimension - Strip Length inch	1 3/8

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Size Range	8 AWG-350 kcmil

Conductor - Copper Str Size	12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	12 AWG-350 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)