



VG1

by Burndy
Catalog ID: VG1

Prop 65 Notice

Cu Alloy Vise Connectors, #6 - #10 Sol

Product Details

General

Connector Type	Stud Connector
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	VISEIT™
UPC	781810475119

Dimensions

Bolt Size	3/8 in
Dimension - B Length fraction	46/73 in
Dimension - B Length inch	0.63 in
Dimension - Pad Width inch	0.75 in
Dimension - Pin Diameter fraction	47/50 in
Dimension - Pin Diameter inch	0.94 in

Conductor Related

Conductor - Copper Solid Run	#10 - #6
Conductor - Copper Solid Run Range	#10 - #6
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Solid Tap	#10 - #6
Conductor - Copper Solid Tap Range	#10 - #6
Conductor - Copper Str Run	#10 - # 6
Conductor - Copper Str Run Range	#10 - # 6
Conductor - Copper Str Tap	#10 - #6
Conductor - Copper Str Tap Range	#10 - #6

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)