



VG3

by Burndy
Catalog ID: VG3

Prop 65 Notice

Cu Alloy Vise Connectors, #2 - #6 Sol

Easy to install and will not swivel. The interlocking will not rotate out of the body. Supplied with hex head bolts, VG1 has a slotted hex bolt.

Product Details

General

Application	Accommodates a wide range of conductors
Connector Type	Stud Connector
Construction Material - Main	Copper
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	WISEIT™
Type	VG
UPC	781810475133

Dimensions

Bolt Size	9/16 in
Dimension - B Length fraction	39/47 in
Dimension - B Length inch	0.83 in
Dimension - Pad Width inch	0.94 in
Dimension - Pin Diameter fraction	49/50 in
Dimension - Pin Diameter inch	0.98 in

Conductor Related

Conductor - Copper Solid Run	6 - 2
Conductor - Copper Solid Run Range	6 - 2
Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	6 AWG-2 AWG
Conductor - Copper Solid Tap	6 - 2
Conductor - Copper Solid Tap Range	6 - 2
Conductor - Copper Str Run	6 - 2
Conductor - Copper Str Run Range	6 - 2
Conductor - Copper Str Tap	6 - 2
Conductor - Copper Str Tap Range	6 - 2

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	250 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)