



VP2828

by Burndy
Catalog ID: VP2828

Prop 65 Notice

1/0 STR. - 4/0 STR. GROOVE A GROOVE B

Product Details

General

Connector Type	V-Bolt
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013571

Dimensions

Dimension - Height fraction	2-1/8 in
Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Conductor Related

Conductor - Copper Str Size A	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size A Range	1/0 -4/0 AWG
Conductor - Copper Str Size B	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size B Range	1/0 -4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)