



## VP3430

by Burndy  
Catalog ID: VP3430

Prop 65 Notice

300 - 500 KCMIL GROOVE A GROOVE B

## Product Details

### General

Connector Type	V-Bolt
Material	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013595

### Dimensions

Dimension - Height fraction	3-1/8 in
Dimension - Height inch	3.19 in
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.25 in
Dimension - Width fraction	2-1/2 in
Dimension - Width inch	2.50 in
Dimension - Width mm	64 mm

### Conductor Related

Conductor - Copper Str Size A	300;350;400;450;500
Conductor - Copper Str Size A Range	300-500
Conductor - Copper Str Size B	1/0;2/0;3/0;4/0;250;300
Conductor - Copper Str Size B Range	1/0-300

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	8
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)