



VT2C2C

by Burndy
Catalog ID: VT2C2C

High Cu Alloy VARITAP T-Connector, Bolted, Cable to Cable, #8 Sol - #2 Str(Run), #8 Sol - #2 Str(Tap)

Product Details

General

Application	Substation
Connector Type	T-Connector
Installation Torque Recommended Run in-lb	275 LBS/in
Installation Torque Recommended Tap in-lb	275 LBS/in
Installation Torque Recommended in-lb	0.57 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Trade Name	VARITAP™
Type	Bolted Tees
UPC	781810808009
UPC 12 Digit	7818108080099

Dimensions

Dimension - Height fraction	1-3/8
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.31 in
Dimension - Width fraction	1-5/16 in
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Cable
Conductor - Copper Solid Run	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG

Conductor - Copper Solid Run Range	8 AWG-2 AWG
Conductor - Copper Solid Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap Range	8 AWG-2 AWG
Conductor - Copper Str Run	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	8 AWG-2 AWG
Conductor - Copper Str Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	8 AWG-2 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)