



VT4428

by Burndy
Catalog ID: VT4428

Prop 65 Notice

High Cu Alloy VARITAP T-Connector, Bolted, Cable to Cable, 750 - 1000 Kcmil(Run), 1/0 Str - 4/0 Str(Tap)

Product Details

General

Application	Substation
Connector Type	T-Connector
Installation Torque Recommended Run in-lb	500 LBS/in
Installation Torque Recommended Tap in-lb	250 LBS/in
Installation Torque Recommended in-lb	2.7 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Trade Name	VARITAP™
Type	Bolted Tees
UPC	781810005668
UPC 12 Digit	7818100056688

Dimensions

Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	105 mm
Dimension - Length Overall inch	4.13 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.69 in
Dimension - Width mm	43 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Cable
------------------------------------	----------------

Conductor - Copper Solid Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1/0 -4/0 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)