



VVA342N

by Burndy
Catalog ID: VVA342N

Prop 65 Notice

CU Varilug, Cable Range: 300 Kcmil - 500 Kcmil

Product Details

General

Application	Substation
Clamping Element Design	V Bolt
Connector Type	Terminal
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Clamping Elements	2
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.30 x 3.06 - 2 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Trade Name	VARILUG™
Type	Bolted Lugs & Terminals
UPC	781810005712
UPC 12 Digit	7818100057122

Dimensions

Dimension - B Length inch	1.31 in
Dimension - D inch	3.06 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	3-11/32 in
Dimension - Height inch	2.56 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	175 mm
Dimension - Length Overall inch	6.88 in
Dimension - N inch	0.62 in

Dimension - Pad Size inch	1.30 x 3.06
Dimension - Pad Width inch	1.30 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	2.22 in
Dimension - Width mm	56 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)